

# muRata Capacitor Data Sheet

## DHRB34C331M2BB

"#" indicates a package specification code.



Last Time Buy Date: 30 Sep 2019      Date of discontinuation: 30 Sep 2020

< List of part numbers with package codes >  
DHRB34C331M2BB

### Shape

L size or outer diameter D (mm)	12.0 mm max.
T size	8.2 mm max.
Lead spacing F	9.5 ±2.0mm
Lead diameter d	0.65 ±0.05mm
Paint dripping e	4.0mm max.

### References

Packaging	Specifications	Minimum quantity
B	Packing in bulk	100

### Specifications

Capacitance	330pF ±20%
Rated voltage	15kVdc
Temperature characteristics (complied standard)	B(JIS)
Capacitance change rate	±10%
Temperature range of temperature characteristics	-25 to 85°C
Operating temperature range	-25 to 100°C

1 of 1

#### ⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.